

SRP - 350



RECEIPT PRINTER

Operator's Manual

All specifications are subjected to change without notice

Warning - U.S.

This equipment has been tested and found to comply with the limits for a Class A digital device pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates uses, and can radiate radio frequency energy and , if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

Notice - Canada

This Apparatus complies with class "A" limits for radio interference as specified in the Canadian department of communications radio interference regulations.

Get appareil est conforme aux normes class "A" d'interference radio tel que specifier par ministre canadien des communications dans les reglements d'interference radio.

Caution

Some semiconductor devices are easily damaged by static electricity. You should turn the printer "OFF", before you connect or remove the cables on the rear side, in order to guard the printer against the static electricity. If the printer is damaged by the static electricity, you should turn the printer "OFF".

INTRODUCTION

The SRP-350, SRP-350S, SRP-350P and SRP-350U Roll Printer are designed for use with electronic instruments such as system ECR, POS, banking equipment, computer peripheral equipment, etc.

The main features of the printer are as follows:

1. High speed printing : 35.5(1/6" Feed) lines per second.
2. Low noise thermal printing.
3. RS-232(SRP-350), RS-485(SRP-350S), Parallel(SRP-350P), USB(SRP-350U)
4. The data buffer allows the unit to receive print data even during printing.
5. Peripheral units drive circuit enables control of external devices such as cash drawer.
6. Characters can be scaled up to 64 times compared to it's original size.
7. Bar code printing is possible by using a bar code command.
8. Different print densities can be selected by DIP switches.

Please be sure to read the instruction in this manual carefully before using your new SRP-350/SRP-350P.

NOTE : The socket-outlet shall be near the equipment and it shall be easy accessible.

Table of Contents

CHAPTER 1. SETTING UP THE PRINTER	4
1-1. UNPACKING	4
1-2. CONNECTING THE CABLES	5
1-3. CONNECTING THE COMPUTER.....	6
1-4. CONNECTING THE DRAWER.....	6
1-5. CONNECTING THE POWER SUPPLY.....	7
1-6. INSTALLING OR REPLACING THE PAPER ROLL	8
1-7. ADJUSTMENTS AND SETTINGS	10
1-8. USING THE PRINTER	11
CHAPTER 2. HEXADECIMAL DUMPING	14
CHAPTER 3. THE SELF TEST	15
CHAPTER 4. CODE TABLE	16
CHAPTER 5. CONTROL COMMANDS LIST	24
APPENDIX	27
A. STAR MODE COMMAND SUMMARY	27
B. CONNECTORS	30
Interface Connector	31
Drawer Connector	34
C. NOTES	34
D. SPECIFICATION.....	35

[Click here to download the full manual at THE-CHECKOUT-TECH.COM](http://THE-CHECKOUT-TECH.COM)